Containment Big Bag Filling

JEL SmartCon BS

► JEL SmartCon BS

With the JEL SmartCon BS attachment system, big bags with foil liners can be easily and safely filled under containment conditions up to OEB 4. Thanks to the high degree of automation, the system is very easy to operate and operating errors and the resulting breaks in containment can be reliably prevented.

Operation

The liner of the big bag to be filled is pre-attached to the docking system. The liner of the previously filled big bag can be comfortably and safely removed with the engagement connection with an endless liner system. The liner of the big bag to be filled is then automatically connected to the docking system with the pressure plate and pneumatic seals and the filling starts. After the filling has finished, the connected liner is tied up with special cable ties and separated from the docking system. The operating personnel are supported by a control system that specifies all the work steps.

LENGELSMANN AG The Experts for bulk solids processes

Areas of application


Chemicals	Plastics	Pharma- ceuticals	Foodstuffs	Similar industries
•	•	•	•	•

► OEB-level

1	2	3	4	5	6
•	•	•	•	0	0

▶ Big bag applications

Big bag filling	Big bag emptying	
٠	0	



Containment Big Bag Filling

JEL SmartCon BS

Design

- The inlet can be tied up using special cable ties and pincers
- Generously-sized engagement connection with endless liner system
- Materials: Stainless steel 1.4301 (standard), silicone seals (other materials available upon request)
- A variety of surface treatments are available (standard: glass bead blasted)
- Inlet length: min. 700 mm
- Optional: Pressure test before the filling to detect any damage to the liner
- Available in ATEX designs for gas and dust

Convincing facts



Protection of operating personnel (exposure) and products (cross-contamination)



Simple operation and quick container change



Little human intervention needed thanks to the high degree of automation



No operating errors thanks to the intuitive control concept



Optional leakproofness test detects any damage to the foil liner before the filling



DIMENSIONS (MM)

Continuously dust-tight process


Technical details


Maximum substance concentration during the filling: < 10 μ g/m³ (corresponds to OEB level 4).

MACHINE

Compressed air Voltage Frequency Protection class Model В L1 L2 6 bar* 230 V 50 Hz IP54 JEL SmartCon BS 635 690 205 460

*3 bar upon request





Pressure plate open

Your contact person

You have questions or need a non-binding quotation? Our experts are happy to help you!

J. Engelsmann AG

Frankenthaler Str. 137-141 D-67059 Ludwigshafen Tel.: +49 (0)621-59002-0 Fax: +49 (0)621-59002-550 info@engelsmann.de www.engelsmann.com

Product page JEL SmartCon BS

Clever Big Bag Handling